

1. Product- And Company	Issue Date	30.01.2007
1.1 Trade Name	<b>KM-2560 / 3060</b>	
1.2 Company	<i>Kyoceramita Europe B.V., Otto-Hahn Strasse 12, D-40670 Meerbusch</i>	
1.3 Phone	<i>+49-(0)2159-928-921</i>	
2. Safety Approvals	<i>Safety 73/23/EEC EMC 89/336/EEC</i>	
3. Environment Approvals	<i>Meet the criteria of the Blue Angel Mark RAL UZ-122</i>	
4. Power Consumption	<i>Maximum Rated: 1370 W Copy Mode: 560 W Sleep Mode: 8.7 W Stand By Mode: 160 W, Off Mode: &lt; 0.1 W</i>	
5. Installation Notes	<i>The machine should be placed more than 10 cm from the wall with a minimum of left 60 cm/right 60 cm/front 100cm space for operation and maintenance. Sufficient ventilation should be provided. The machine should not be placed in a dusty room or where ammonia gas is in use.</i>	
6. Room Humidity	<i>20 % – 80 %</i>	
7. Room Temperature	<i>10.0 °C – 32.5 °C</i>	
8. Noise Level	<i>Copying: 67.0 / 68.7 dB(A) Lwad RAL UZ 122 Stand By: 34.9 / 34.8 dB(A) Lpa RAL UZ 122</i>	
9. Light Source	<i>Exposure Original: Noble Gas Lamp Exposure Drum: Semiconductor Laser</i>	
10. Emissions	<i>Ozone: 0.7 mg/h RAL UZ 122 Fine Dust: &lt; 0.45 mg/h RAL UZ 122 Styrene: &lt; 0.3 mg/h RAL UZ 122 Benzene: 0.02 mg/h RAL UZ 122 TVOC: 8.5 mg/h RAL UZ 122</i>	
11. Others		